

Manual Supplement

Manual Title:	7340 Users Guide	Supplement Issue:	4
Print Date:	January 2013	Issue Date:	1/19
Revision/Date:		Page Count:	1

This supplement contains information necessary to ensure the accuracy of the above manual.
This manual is distributed as an electronic manual on the following CD-ROM:

CD Title:	7340
CD Rev. & Date:	2/2013
CD PN:	3750939

Change #1

On page 12, after the last bullet in the **Environmental Conditions** section, add:

Note

The Product can show some control sensitivity to moderate or severe electromagnetic fields or conducted interference of certain frequencies. In the presence of radiated EM disturbances, with frequencies of 250 MHz to 400 MHz and with amplitude >1 V/m to a maximum of 3 V/m, add 0.0025 °C to the stability specification. Stability is not guaranteed if amplitude is >3 V/m. When subject to conducted disturbances of 8 MHz to 80 MHz, and amplitude >3 V, add 0.005 °C to the stability specification.

Change #2, 518

On page 12, under the **Environmental Conditions**, replace the 1st and 2nd bullets with:

- ambient temperature range: 5 °C to 35 °C (41 °F to 95 °F)
- ambient relative humidity: maximum 80 % for temperatures <31 °C decreasing linearly to 50 % at 35 °C

Change #3, 535

On page 11, under **Specifications**, replace the **Power** row with:

Power 115 V ac (±10 %), 60 Hz, 15 A [230 V ac (±10 %), 50 Hz, 8 A optional], 1400 VA

⚠ Caution

If the voltage is outside ±10 %, the compressor may be damaged. Check the back panel label for the correct voltage and frequency prior to energizing the unit.

Change #4, 640

On page 11, under **Specifications**, replace the **Refrigeration** row with:

Refrigeration R-410A single stage

On page 33, under **8.6 Refrigeration**, change:

From: R-507

To: R-410A